

Coaxial Nozzles for Electroma- gnetic Single Nozzle Encap- sulation Units



Nisco Engineering AG
Wehntalerstrasse 562
CH-8046 Zurich, Switzerland

Tel: +41 44 380 06 30
Fax: +41 44 380 06 31
E-mail: mailbox@nisco.ch
<http://www.nisco.ch>

The coaxial nozzles consist of two sub-nozzles allocated in a coaxial way. Both nozzles are made in stainless steel 1.4435(AISI316L).




The nozzles can be used for following Nisco encapsulation units:

- VAR D Professional line, VAR D classic, VAR D Generation II
- VAR B especial adaptation piece is required

Special equipment is available, for example a heated head to encapsulate water in wax or fat.

The nozzles are available with material certificates for qualification purpose.

On the following picture you see drops of sunflower oil encapsulated in 2% Alginate (Sigma, low viscosity) sterile filtered.



Possible combinations:

id 0.150 with ID 0.300	id 0.200 with ID 0.600
id 0.150 with ID 0.400	id 0.300 with ID 0.400
id 0.150 with ID 0.500	id 0.300 with ID 0.500
id 0.150 with ID 0.600	id 0.300 with ID 0.600
id 0.200 with ID 0.300	id 0.400 with ID 0.500
id 0.200 with ID 0.400	id 0.400 with ID 0.600
id 0.200 with ID 0.500	