Flow control unit with needle valve (for the VAR J1)

Nisco article No. A 01063

Complete flow unit mounted on a holder with 12mm bar and double socket to fix it on a lab support with 12mm bar. The flow control unit consists of:

Pressure limiter

Inlet pressurized oil free air 5-10barg Outlet 1.5barg

Pressure limiter

Needle Valve range 0..10L/min with potentiometer type manual drive.



Nisco Engineering Inc.

Wehntalerstrasse 562 CH-8046 Zurich, Switzerland

Tel: +41 44 380 06 30 Fax: +41 44 380 06 31 e-mail: mailbox@nisco.ch http://www.nisco.ch



Inlet Air hose

inner diameter 4mm outer diameter 6mm (outside calibrated)
On the picture a black PE hose has been

used.

Outgoing hose

inner diameter 2mm.
On the picture a silicone hose has been used.